UHF TV Klystron Amplifier

- Water/Vapor Cooled
- High Power Output
- Electromagnet Focusing
- Very High Gain
- Easy to Install and Operate
- Long Life, High Reliability
- Modulating Anode permits Integral Cavity Construction both visual and aural application with a single beam supply

General Data

| Electrical: | |
|-------------|--|
| Eroouone | |

Heater (dc or 50-60 Hz):

 Voltage^a
 6.0 ± 0.5
 V

 Current @ 6.0 V, typical
 16.4
 A

Mechanical:

Mounting Position Vertical, cathode down

Dimensions, Maximum:

Weight, Approximate:

Inlet Coolant Connector Mates with Hansen LL3-H21
Outlet Coolant Connector Mates with Hansen LL6-H31

Steam Outlet See Dimensional Outline

Electrical Connections:

Thermocouple:

Chromel Pin H Cannon Rec.^c
Alumel Pin J Cannon Rec.^c

| Body | Pin E C | annon R | ec.c | |
|--|----------|----------------|------------------------|--|
| Modulating Anode See [| Dimensi | onal Ou | tline | |
| Heater-Cathode See I | Dimensi | onal Ou | tline | |
| Heater See I | Dimensi | onal Ou | tline | |
| Interlock No.1 Pins A a | ind B, C | annon F | Rec.C | |
| Interlock No.2 Pins C a Thermal: | | | | |
| Collector Temp. (max.) | | | °C | |
| Body Temperature (max.) | | 100 | oC. | |
| Electron Gun Insulator Temp. (max.) | | 250 | °C | |
| Storage Temp.d (min.) | | -65 | °C | |
| Coolant Requirements: | | | | |
| Collector and Body | | | | |
| Water flow (min.) | | | | |
| Inlet water temperature (max.) | | 70 | oC | |
| Electron Gun | | | | |
| Forced air flow ^e (min.) | (24 1/s) | 50 | cfm | |
| Water Pressure Differential for Typical Flow of 2.1 gpm (max.) | | ∫3.5 kg/ 50 | cm ² psi | |
| | | 4.2 kg | _{/cm} 2 | |
| Water Pressure at any Inlet (max.) | | 60 | psi | |
| Maximum Ratings, Absolute-Maximum Values | | | | |
| Beam Voltage, DC | 20 | max. | kV | |
| Beam Current, DC | 5.5 | max. | Α | |
| Body Current, DC | 250 | max. | mΑ | |
| Modulating Anode Voltage, DC | 20 | max. | kV | |
| Load VSWR | 1.5 | :1.0 | | |
| Typical Operation, UHF Television Service | e | | | |
| (Visual 699.25 MHz, Aural 703.75 MHz) | | | | |
| | Visual A | Aural | | |
| Collector Voltage, DCf | 0 | 0 | V | |
| Body Voltage, DC | 0 | 0 | V | |
| Beam Current, DC | 4.7 | 2.4 | Α | |
| Body Current, DC9 | 70 | 15 | mΑ | |
| Modulating Anode Voltage, DC | 0 | -6 | kV | |
| Modulating Anode Current, DC | 1.5 | 1.0 | mΑ | |
| Cathode Voltage, DC | -18 | -18 | kV | |

| Focusing Current, DC (Typical With RCA-AJ2168 Electromagnet) | 28 | 28 | Α |
|--|-------|-------|----|
| Load VSWR | 1.1:1 | 1.1:1 | _ |
| Drive Power for Visual Peak-of- Sync or Aural CW | 10 | 1.1 | w |
| Output, for Visual Peak-of-Sync or Aural CW | 31 | 12 | kW |
| Gain | 35 | 40 | dB |
| Efficiency | 37 | 28 | % |

- Careful attention to maintaining the minimum value of filament voltage consistent with adequate emission will result in conserving the life of the tube.
- b Pins F and G must always be used in parallel.
- c Type CA22365-2729 Cannon Receptacle.
- d All water must be removed from the coolant course during storage and shipping.
- e Cooling-air blower must be directed toward the electron gun and located within a distance of 24 inches.
- f A dc ammeter makes the connection between the collector and ground.
- 9 The body is connected directly to ground. Body current is measured in the ground leg of the beam power supply.


Operating Considerations

Typical operating coil currents are noted under "Typical Operation" data section in this data sheet.

It is recommended that the coil coolant flow start before the application of any coil voltage and preferably continue for five minutes after the removal of voltages. Interlocking of the coolant flow with the klystron beam and modulatinganode voltages and coil voltages is highly recommended to prevent tube and coil damage in the event of inadequate coolant flow.

The use of a solid-state diode connected in parallel with the electromagnet is recommended to prevent excessive transient voltage build-up in the event of coil current interruptions. Connections should be made so the coil current will flow through the diode when the polarity of the normal coil voltage becomes reversed.

Dimensional Outline - Klystron



Pin Connections - Voltage Socket

A Jumpered F Collector*
G Collector*

C Jumpered H Thermocouple (Chromet)
J Thermocouple (Alumet)


E Body (Ground) *Always use pins F and G in parallel.

Tabulated Dimensions for Klystron

| Dim. | Value - Inches | Value – Millimeters |
|------|--------------------|---------------------|
| Α | 45.56 <u>+</u> .32 | 1157 <u>+</u> 8 |
| В | 16.33 ± .06 | 414.8 <u>+</u> 1.5 |
| С | 1.50 <u>+</u> .01 | 38.10 <u>+</u> .25 |
| D | 13.00 Max. | 330.2 Max. |
| E | 11.00 <u>+</u> .12 | 279.4 <u>+</u> 3.0 |
| F | 0.23 <u>+</u> .04 | 5.8 <u>+</u> 1.0 |
| G | 12.40 Max. | 315.0 Max. |
| н | 6.40 <u>+</u> .04 | 162.6 <u>+</u> 1.0 |
| J | 0.50 <u>+</u> .02 | 12.70 <u>+</u> .51 |
| κ | 38.67 <u>+</u> .25 | 982.2 <u>+</u> 6.4 |
| М | 18.66 <u>+</u> .08 | 474.0 <u>+</u> 2.0 |
| N | 15.74 <u>+</u> .06 | 399.8 <u>+</u> 1.5 |
| Р | 11.50 <u>+</u> .05 | 292.1 <u>+</u> 1.3 |
| R | 7.15 <u>+</u> .04 | 181.6 <u>+</u> 1.0 |
| S | 2.82 <u>+</u> .03 | 72.4 <u>+</u> .8 |
| T | 5.76 Max. | 14.63 Max. |
| U | 0.04 Ref. | 1.0 Ref. |
| V | 5.00 <u>+</u> .01 | 127.00 <u>+</u> .25 |
| W | 0.19 <u>+</u> .01 | 4.83 <u>+</u> .25 |
| X | 6.89 ± .07 | 175.0 <u>+</u> 1.8 |
| Υ | 0.69 ± .05 | 17.5 <u>+</u> 1.3 |
| Z | 5.00 ± .03 | 127.0 <u>+</u> .8 |

Notes:

- 1. RF Input Jack, UG-22 B/U mates with UG-21 D/U.
- Channel tuning screws. These screws have a 5/16 inch hex socket head.
- Tube rollers mate with roller guides in the RCA AJ2168 Electromagnet.
- 4. Inlet Water Connector mates with Hansen LL3-H21 Connector.
- Reference Surface corresponds with electromagnet reference surface when installed.
- 6. Drain Connector mates with Hansen LL6-H32 Connector.
- 7. Cannon Receptacle CA22365-2729. Mates with Cannon Plug 24-20.



Personnel Safety

The high voltages and microwave radiations from this device can be dangerous to life. High voltage shielding and interlock precautions must be taken and all rf connections must be tightly closed and rf terminals adequately shielded. This device, in operation, may produce X-radiation which can constitute a health hazard. Shielding or other precautions may be required.

Tabulated Dimensions for Electromagnet

| Dim. | Value – Inches | Value - Millimeters |
|------|---------------------------|---------------------|
| Α | 2.87 <u>+</u> .03 | 72.9 <u>+</u> .8 |
| В | 7.25 <u>+</u> .03 | 184.2 <u>+</u> .8 |
| С | 11.60 ± .03 | |
| D | 15.79 ± .03 | 401.1 <u>+</u> .8 |
| E | 0.50 ± .02 | 12.7 <u>+</u> .5 |
| F | 19.28 <u>+</u> .05 | 489.7 <u>+</u> 1.3 |
| G | 1.76 ± .06 | 44.7 <u>+</u> 1.5 |
| н | 10.00 ± .03 | 254.0 <u>+</u> .8 |
| J | 12.79 <u>+</u> .03 | |
| K | 3.16 <u>+</u> .06 | 80.3 <u>+</u> 1.5 |
| L | 4.00 <u>+</u> .03 | 101.6 <u>+</u> .8 |
| | 4.50 <u>+</u> .03 | |
| | 3.00 ± .03 | |
| P | 7. 00 <u>+</u> .03 | 177.8 <u>+</u> .8 |
| R | 16.00 <u>+</u> .03 | 406.4 <u>+</u> .8 |
| S | 17.00 Max. | 431.8 Max. |
| Т | 1.00 <u>+</u> .03 | 25.4 <u>+</u> .8 |
| V | 5.60 <u>+</u> .03 | 142.2 <u>+</u> .8 |
| w | 12.80 ± .05 | 325.1 <u>+</u> 1.3 |
| X | 10.68 ± .05 | 271.3 <u>+</u> 1.3 |

General Information Cooling

The electron gun is cooled by forced air directed at the cathode-seal area. Air flow must be at least 50 cfm. (24.0 l/sec). The remainder of the tube is cooled by water/vapor system with water cooling the resonators and drift-tube sections and vapor cooling the collector.

The use of distilled water is essential. The liquid flow must start before application of any voltages and preferably should continue for five minutes after removal of voltages. It is recommended that the liquid flow through each of the cooled elements be interlocked with the beam supply to prevent damage to the tube in case of cooling failure.

A steam exhaust sleeve must be provided for the top of the klystron boiler. A flexible, neoprene type is recommended.



The sleeve is placed over the lip provided at the top of the boiler (see Dimensional Outline) and clamped securely in place for a water-tight connection.

Electrical Connections to Tube Terminals

Connections to the Heater, Heater-Cathode and Modulating Anode Terminals (see Dimensional Outline) are made with preformed finger stock or knife blade type fuse clips. Care should be taken when making these connections not to place excessive stress on the ceramic-to-metal seals.

Protection Circuits

Protection circuits serve a threefold purpose: safety of personnel, protection of the tube and protection of tube circuits. Consult Application Note AN4206 for complete information on protection circuits required.

A means of protecting the klystron against damage which would result from failure of the collector vapor cooling system is provided by an integral chromel-alumel thermocouple with terminals at the Cannon Receptacle.

RCA AJ2168 Electromagnet

Congral Data

The RCA 8826 klystron is designed to be mounted in and its beam focused by the water-cooled, single-coil electromagnet, RCA-AJ2168. The exposed surfaces of the electromagnet are treated by painting or plating to resist corrosion.

| General Data | | | | |
|---|------------|-------------------|--------|--------|
| Voltage, DC (max.) | | | 35 | V |
| Current, DC (max.) | | | | Α |
| Dimensions | See Di | mensio | onal O | utline |
| Weight (Approx.) | | | | lbs |
| | Crated (14 | 15 kg) | 320 | lbs |
| Cooling: | • | | | |
| Water flow, minimum | (0.0) | 63 I/s) | 1 | gpm |
| Inlet temperature, maximum | | | 70° | С |
| Maximum water pressure differential for typical flow (gauge). | (3.5 k | g/cm ² | 9) 50 | psi |
| Maximum water pressure at | (4.2 k | a/cm ² | 2) 60 | psi |